



**Inch table**

Dimensions in: inches - *millimeters*

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Thread	<sup>3</sup> Length l	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>
1.69 42.9	5/16 x 18	1.00 25.4	0.67 17.0	1.14 29.0	0.43 10.9
2.09 53.1	3/8 x 16	1.50 38.1	0.75 19.0	1.34 34.0	0.51 13.0

**Metric table**

Dimensions in: millimeters - *inches*

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Thread	<sup>3</sup> Length l	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>			
43 1.69	M 6	16 0.63	20 0.79	25 0.98	30 1.18	17 0.67	29 1.14	11 0.43
43 1.69	M 8	16 0.63	20 0.79	25 0.98	30 1.18	17 0.67	29 1.14	11 0.43
53 2.09	M 8	16 0.63	20 0.79	30 1.18	40 1.57	19 0.75	34 1.34	13 0.51
53 2.09	M 10	20 0.79	30 1.18	40 1.57	50 1.97	19 0.75	34 1.34	13 0.51
66 2.60	M 10	20 0.79	30 1.18	40 1.57	50 1.97	21.5 0.85	38.5 1.52	15.5 0.61
66 2.60	M 12	30 1.18	40 1.57	50 1.97	-	21.5 0.85	38.5 1.52	15.5 0.61
77 3.03	M 12	30 1.18	40 1.57	50 1.97	-	26 1.02	46 1.81	21 0.83

**Specification**

- Five-lobed knob  
Plastic  
Technopolymer (Polypropylene PP)
- Softline coating
  - Elastomer (TPE) 70 shore A
  - Chemically bonded with the plastic core
  - FDA compliant plastic granulate
  - Temperature resistant up to 175 °F (80 °C)
  - Black, matte finish
- Color of the cover cap:  
Black, RAL 9005, matte finish
- Threaded stud  
Steel, zinc plated, blue passivated finish
- RoHS compliant

**Information**

The Softline coating makes the GN 5337.6 five-lobed knobs particularly user-friendly and ergonomic. The **soft, slip-proof** contact area improves the contact both in hot (hand perspiration) and in dry ambient conditions, in the event of oily surfaces and even high or low temperatures. The use of five-lobed knobs with threaded stud is recommended particularly when heavy duty clamping is required.

**On request**

- Cover caps in other colors

<b>How to order</b> <b>EN 5337.6-53-M10-30</b>	<sup>1</sup>	Handle diameter d <sub>1</sub>
	<sup>2</sup>	Thread d <sub>2</sub>
	<sup>3</sup>	Length l

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4