



Metric



elesa
Original design M.943

Metric table

| ¹ $l_1 \pm 0.5$ | ² d_1 Thread | ² d_2 Bore | b | h | l_2 | l_3 | s | t min. |
|----------------------------|------------------------------|----------------------------|--------------|--------------|-------------|---------------|------------|-------------|
| 88 3.46 | M 5 | B 4.5 | 13.5 0.53 | 36.5 1.44 | 112 4.41 | 74.5 2.93 | 9 0.35 | 10 0.39 |
| 120 4.72 | M 5 | B 4.5 | 15 0.59 | 42 1.65 | 144 5.67 | 106.5 4.19 | 11 0.43 | 10 0.39 |

Dimensions in: millimeters / inches

Specification

Handle

- Plastic, Polyamid (PA)
- Glass fiber reinforced
- Operating temperature
-22 °F to 266 °F (-30 °C to +130 °C)
- Black, matte finish

Tapped insert

Brass

RoHS

On request

Various metric size fasteners and kit packaging

The dimensions of cabinet U-handles EN 627 are suitable for 19" rack and enclosure layout.

They have been designed for mounting via the threaded inserts or via sheet metal screws with thread size ST 4.8, such as DIN ISO 7049 pan head screws. Maximum recommended tightening torque is 5 Nm.

Resistant to solvents, oils, grease and other chemical agents.

see also...

| | Page |
|---|------|
| GN 427 Cabinet U-Handles (Aluminum, Ellipse Shaped Profile) | QVX |
| GN 427.5 Cabinet U-Handles (Stainless Steel, Ellipse Shaped Profile) | QVX |
| GN 425 Cabinet U-Handles (Aluminium / Stainless Steel) | QVX |

Technical Information

| | |
|-------------------------|-----|
| Strength Values | QVX |
| Plastic Characteristics | QVX |

How to order

EN 627-88-M5

- ¹ Length l_1
- ² Thread d_1 (Bore d_2)

1.1
1.2
1.3
1.4
2.2
2.3
2.4

