



Metric table



Dimensions in: millimeters - inches

d ₁	d ₂	d ₃	l ₁	l ₂	l ₃ min.
M 10	18 <i>0.71</i>	8 <i>0.31</i>	80 <i>3.15</i>	60 <i>2.36</i>	20 <i>0.79</i>
M 12	20 <i>0.79</i>	10 <i>0.39</i>	100 <i>3.94</i>	70 <i>2.76</i>	25 <i>0.98</i>
M 16	24 <i>0.94</i>	12 <i>0.47</i>	120 <i>4.72</i>	85 <i>3.35</i>	35 <i>1.38</i>
M 20	30 <i>1.18</i>	16 <i>0.63</i>	140 <i>5.51</i>	95 <i>3.74</i>	40 <i>1.57</i>

Specification

- Body
Steel, blackened finish
- [RoHS compliant](#)

Information

DIN 6305 tommy nuts are an ideal choice over a plastic T-knob where a higher clamping torque is required.

see also...

- [Quick Release Toggle Nuts GN 6305.1 \(Steel, Zinc Plated\)](#) → page QVX
- [Tommy Nuts DIN 6307 \(Steel, with Movable Bar\)](#) → page QVX

How to order



DIN 6305-M16

1 Thread d₁