



SS Stainless Steel

- 3 Type**
- E** With tapped blind bore
  - D** With tapped through bore
  - C** With plain blind bore, tol. H7

**Specification**

- Stainless steel precision casting AISI CF-8
  - Matte shot-blasted finish **MT**
  - Highly polished finish **PL**  
(only available in Type D, E in metric sizes)
- *Cross Holes GN 110* → page 2042
- *ISO Fundamental Tolerances* → page 2129
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

**On request**

- Version with convex top and sides in highly polished finish
- Polished finish available for inch size tapped knobs
- Other modifications such as inch or metric tapped holes, blind or through bores, cross holes, set screw holes and threaded studs

**Information**

GN 5339.5 triangular knobs were specially designed for use on machinery in the food industry. The smooth and enclosed areas as well as the corner radii comply with the requirements of hygiene standards.

With an elegant ergonomical design, these knobs also withstand a relatively high torque.

**see also...**

- *Star Knobs GN 5334 (Stainless Steel)* → page 616
- *Star Knobs DIN 6336 (Stainless Steel)* → page 572
- *Hand Knobs DIN 6335 (Stainless Steel)* → page 626
- *Star Knobs GN 5335 (Stainless Steel)* → page 620
- *Wing Nuts GN 834 (Stainless Steel)* → page 676

How to order (Inch)	1 Handle diameter $d_1$
1 2 3 4	2 Thread $d_2$
<b>GN 5339.5-32-10X32-E-MT</b>	3 Type
	4 Finish
How to order (Metric)	1 Handle diameter $d_1$
1 2 3 4	2 Thread $d_2$ (Bore $d_3$ )
<b>GN 5339.5-50-M10-D-PL</b>	3 Type
	4 Finish

### Inch table

Dimensions in: inches - millimeters

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Thread Type E	d <sub>4</sub>	h <sub>1</sub> ≈	h <sub>2</sub> ≈	t <sub>1</sub> min.
1.26 32	10 x 32	0.47 12	0.83 21	0.47 12	0.39 10
1.26 32	1/4 x 20	0.47 12	0.83 21	0.47 12	0.47 12
1.57 40	1/4 x 20	0.55 14	1.02 26	0.55 14	0.47 12
1.57 40	5/16 x 18	0.55 14	1.02 26	0.55 14	0.59 15
1.97 50	5/16 x 18	0.71 18	1.30 33	0.75 19	0.59 15
1.97 50	3/8 x 16	0.71 18	1.30 33	0.75 19	0.71 18
2.36 60	3/8 x 16	0.79 20	1.61 41	0.91 23	0.71 18
2.36 60	1/2 x 13	0.79 20	1.61 41	0.91 23	0.87 22

### Metric table

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Thread Type E		<sup>2</sup> d <sub>3</sub> H7 Bore Type C	d <sub>4</sub>	h <sub>1</sub> ≈	h <sub>2</sub> ≈	t <sub>1</sub> min.	t <sub>2</sub>
	Type D							
32 1.26	M 5	-	-	12 0.47	21 0.83	12 0.47	10 0.39	-
32 1.26	M 6	M 6	B 6	12 0.47	21 0.83	12 0.47	12 0.47	10 0.39
40 1.57	M 6	-	-	14 0.55	26 1.02	14 0.55	12 0.47	-
40 1.57	M 8	M 8	B 8	14 0.55	26 1.02	14 0.55	15 0.59	13 0.51
50 1.97	M 8	-	-	18 0.71	33 1.30	19 0.75	15 0.59	-
50 1.97	M 10	M 10	B 10	18 0.71	33 1.30	19 0.75	18 0.71	16 0.63
60 2.36	M 10	-	-	20 0.79	41 1.61	23 0.91	18 0.71	-
60 2.36	M 12	M 12	B 12	20 0.79	41 1.61	23 0.91	22 0.87	20 0.79

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

