



**Metric table**



Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	l <sub>1</sub> ≈	l <sub>2</sub>	l <sub>3</sub> ≈
M 10	24 0.94	10.5 0.41	8 0.31	68 2.68	30 1.18	20 0.79
M 12	26 1.02	13 0.51	9 0.35	82 3.23	36 1.42	24.5 0.96
M 16	32 1.26	17 0.67	10 0.39	98 3.86	45 1.77	32 1.26

**Specification**



- Body  
Steel, zinc plated, blue passivated finish **ST**
- Toggle arms  
Butt-welded
- **RoHS compliant**

**On request**

- Stainless steel version

**Information**

GN 6305.1 quick release toggle nuts are used in applications where the knob has to be completely removed after the releasing operation and replaced rapidly for re-clamping.

Place the toggle nut onto the threaded bolt at an oblique angle and straighten out at the desired clamping position. During the clamping action, it engages into the threads of the bolt.

see also...

- *Quick Release Knurled Nuts GN 6303.1* → page 716
- *Quick Release Star Knobs GN 6336.3* → page 717

**How to order**

**GN6305.1-M16-ST**

- 1 Thread d<sub>1</sub>
- 2 Material