



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂	³ Length l	d ₃	h ₁	h ₂
63 2.48	M 8	25 0.98	23 0.91	30.5 1.20	16 0.63
80 3.15	M 10	30 1.18	30.5 1.20	37 1.46	20 0.79
100 3.94	M 12	40 1.57	35 1.38	43 1.69	23 0.91

Specification

- Three-lobed knob
Plastic
Technopolymer (Polyamide PA)
- Coated with a soft elastomer (TPE)
70 shore A
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black, matte finish
- Softline coating is chemically bonded with the plastic core
- Threaded stud
Steel zinc plated, blue passivated finish
- Color of the cover cap (matte finish):
 - DSW Black, RAL 9005
 - DOR Orange, RAL 2004
 - DGR Gray, RAL 7035
 - DGB Yellow, RAL 1021
 - DBL Blue, RAL 5024
 - DRT Red, RAL 3000
 - DGN Green, RAL 6017
- *Plastic Characteristics* → page QVX
- RoHS compliant

Information

The Softline coating of the EN 533.6 three-lobed knobs with threaded stud makes these operating elements particularly “operator friendly” and hence ergonomic.

The soft, non-slip coating improves the contact in both moist (hand perspiration) and in dry conditions, with oily surfaces and at high or very low temperatures.

The use of Softline star knobs is recommended particularly when heavy duty clamping is required.

see also...

- *Three-Lobed Knobs GN 5345* → page QVX
- *Three-Lobed Knobs EN 5330 (Plastic)* → page QVX

How to order	
¹	Handle diameter d ₁
²	Thread d ₂
³	Length l
⁴	Color of the cover cap

EN 533.6-63-M8-25-DBL

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4