



SS Stainless Steel

3 Type

- N** Without cap
- G** With plastic cap, gliding
- R** With rubber cap, non-skid

Metric table

Dimensions in: millimeters - inches

d ₁		h	d ₂ +0.2	e ≈	s	Suitable for DIN 6332 grub screw
Type N / R	Type G					
50 1.97	50 1.97	11.5 0.45	9.2 0.362	3.7 0.15	2 0.08	M 12
50 1.97	50 1.97	13.5 0.53	12.5 0.492	4 0.16	2 0.08	M 16
60 2.36	60 2.36	13.5 0.53	12.5 0.492	4 0.16	2 0.08	M 16
60 2.36	60 2.36	15.5 0.61	16.5 0.650	4.3 0.17	2 0.08	M 20
80 3.15	-	18 0.71	12.5 0.492	8 0.31	2.5 0.10	M 16
80 3.15	-	20 0.79	16.5 0.650	8.3 0.33	2.5 0.10	M 20
100 3.94	-	20 0.79	12.5 0.492	11 0.43	3 0.12	M 16
100 3.94	-	22 0.87	16.5 0.650	11.3 0.44	3 0.12	M 20

Specification

- Body
Stainless steel AISI 304
- Retaining spring
Stainless steel AISI 301
- Cap
Plastic
 - Type **G**
Technopolymer (Polyacetal POM)
White, RAL 9001
 - Type **R**
Elastomer (TPE) ≈ 75 shore A
Black
- [Plastic Characteristics](#) → page 2135
- [Stainless Steel Characteristics](#) → page 2143
- [RoHS compliant](#)

Accessory

- Grub screws DIN 6332 → page 1119

Information

GN 6311.5 thrust pads are used together with screws that have a thrust point (DIN 6332 grub screws) to install and level devices and fixtures.

The innovative design of the retaining spring allows simple mounting and removal of the screw tip to the thrust pad.

The plastic cap (type G / R) prevents damage to delicate surfaces. Due to the large diameter d₁, the contact pressure remains within tolerable limits.

see also...

- [Leveling Feet GN 6311.4 \(Steel\)](#) → page 1476
- [Leveling Feet GN 6311.6 \(Stainless Steel\)](#) → page 1477
- [Thrust Pads GN 6311.1 \(Steel / Stainless Steel\)](#) → page 1123
- [Thrust Pads DIN 6311 \(Steel\)](#) → page 1120

How to order	1	Outer diameter d ₁
	2	Height h
	3	Type
GN 6311.5-50-11.5-R		