



4 Type
A Without clamping bolt

Metric table

Dimensions in: millimeters - inches

1 d_3 Clamp slot size	2 l_1	3 l_6	b	d_2	h_1	h_2 min. - max. (millimeter)	l_2	l_3	Table slot size
11 .43	100 3.94	39 1.54	30 1.18	M 10	15 .59	22 - 51	36 1.42	32 1.26	10
14 .55	125 4.92	49 1.93	40 1.57	M 12	20 .79	28 - 65	44 1.73	40 1.57	12 - 14
18 .71	160 6.30	55 2.17	50 1.97	M 16	25 .98	36 - 75	51.5 2.03	50 1.97	16 - 18
22 .87	200 7.87	69 2.72	60 2.36	M 20	30 1.18	43 - 92	59 2.32	70 2.76	20 - 22

Specification

- Goose neck clamp
Tempered steel, lacquer painted finish
- Knurled adjusting screw
Steel, hardened
Tensile strength class 8.8
- *Strength Values of Screws* → page XYZ
- **RoHS compliant**

Accessory

- DIN 787 T-slot bolt → page XYZ
- DIN 6330 fixture nut → page XYZ
- DIN 6340 heavy duty flat washer → page XYZ
- DIN 508 T-slot nut → page XYZ
- DIN 6379 double-ended threaded stud
→ page XYZ

Information

No. 6316 V adjustable goose neck clamps are particularly suitable for clamping variable height workpieces. The clamping height can be adjusted by means of the adjusting screw (knurled or socket head positions).

Adjusting screw is included as part of the assembly.

see also...

- *Goose Neck Clamps DIN 6316* → page XYZ
- *Adjustable Goose Neck Clamps NO. 6316 V* → page XYZ

How to order

NO.6316V-11-100-39-A

- | | |
|----------|-----------------------|
| 1 | Clamp slot size d_3 |
| 2 | Length l_1 |
| 3 | Length l_6 |
| 4 | Type |