



Universal table

2

Dimensions in: millimeters - inches

Length l	b	h	Nominal magnetic force
55 2.17	22.5 0.89	8.5 0.33	48 N 10.79 lbf

Specification

1

3

- Magnet material
NdFeB **ND**
Neodymium, iron, boron
Temperature resistant up to 176 °F (80 °C)
- Housing
Plastic
 - White, RAL 9003 **WS**
 - Gray, RAL 7040 **GR**
 - Black, RAL 9004 **SW**
 - Red, RAL 3031 **RT**
- RoHS compliant

Information

Retaining magnets GN 53.2 work in combination with the flat, rectangular plastic housing as a system for holding documents, templates, drawings etc. that are used in technical environments. The neodymium magnets used are characterized by a high retaining force.

see also...

- More Information on Retaining Magnets → page QVX
- Retaining Magnets GN 53.1 (Disk-Shaped) → page QVX
- Magnets GN 53.3 / GN 53.4 (Disk-Shaped, with Handle) → page XYZ / QVX

Accessory

- Holding disks GN 70 → page QVX
- Self-adhesive disks GN 70.1 → page QVX

On request

- Other colors
- Magnet material hard ferrite
- With custom imprint

How to order	1 Magnet material
GN 53.2-ND-55-GR	2 Length l
	3 Color

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

