



Inch | Metric

**SS** Stainless Steel

**4** Type

**K** With tapped insert  
**D** With tapped through bore (only available in metric sizes)

**Specification**

- Star knob Plastic Duroplast (Phenolic PF) Black, shiny finish **KU**
- Tapped insert
  - Steel, zinc plated, blue passivated finish —
  - Brass **MS**
  - Stainless steel AISI 304 **NI**
- Star knob Plastic Technopolymer (Polyamide PA) Black, matte finish **KT**
- Tapped insert
  - Steel, zinc plated, blue passivated finish —
  - Stainless steel AISI 303 **NI**
- *Plastic Characteristics* → page 2135
- *Stainless Steel Characteristics* → page 2143
- [RoHS compliant](#)

**Information**

Star knobs DIN 6336 are an economical choice, yet offer top quality and ergonomic styling. The version with stainless steel insert is suitable for certain non-corrosive environment applications.

*see also...*

- *Star Knobs DIN 6336 (Cast Iron / Stainless Steel, Aluminum)* → page 572
- *Star Knobs GN 6336.1 (Phenolic, with Protruding Hub)* → page 574
- *Star Knobs GN 6336.2 (Technopolymer, with Protruding Hub)* → page 574
- *Star Knobs GN 6336.13 (with Loss Protection)* → page 584
- *Star Knobs DIN 6336 with Loss Protection GN 111.7* → page 2046

How to order (Inch, Duroplast, steel insert)	<b>1</b> Material
<b>1</b> <b>2</b> <b>3</b> <b>4</b>	<b>2</b> Handle diameter $d_1$
<b>DIN 6336-KU-50-1/4X20-K</b>	<b>3</b> Thread $d_2$
	<b>4</b> Type

How to order (Metric, Technopolymer, stainless steel insert)	<b>1</b> Material
<b>1</b> <b>2</b> <b>3</b> <b>4</b> <b>5</b>	<b>2</b> Handle diameter $d_1$
<b>DIN 6336-KT-50-M10-K-NI</b>	<b>3</b> Thread $d_2$
	<b>4</b> Type
	<b>5</b> Insert material

### Inch table

Dimensions in: inches - *millimeters*

d <sub>1</sub>	d <sub>2</sub>		d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	t <sub>1</sub> min.		t <sub>2</sub>
	Steel insert Plastic KU Type K	Plastic KT Type K						
0.98 25	-	10 x 32	0.47 12	0.63 16	0.31 8	0.37 9.5	-	
1.26 32	-	1/4 x 20	0.55 14	0.79 20	0.39 10	0.47 12	-	
1.57 40	-	5/16 x 18	0.71 18	0.98 25	0.51 13	0.55 14	0.51 13	
1.97 50	1/4 x 20	3/8 x 16	0.87 22	1.26 32	0.67 17	0.71 18	0.63 16	
2.48 63	5/16 x 18	1/2 x 13	1.02 26	1.57 40	0.83 21	0.87 22	0.79 20	
3.15 80	3/8 x 16	-	1.38 35	1.97 50	0.98 25	1.18 30	-	

### Metric table

Dimensions in: millimeters - *inches*

d <sub>1</sub>	d <sub>2</sub>					d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	t <sub>1</sub> min.			t <sub>2</sub>
	Steel insert Plastic KU Type K	Plastic KT Type K	Plastic KT Type D	MS insert Plastic KU Type K	NI insert Plastic KU / KT Type K				Steel insert MS insert NI insert (KT)	NI insert (KU)		
20 0.79	-	-	-	M 4	-	10 0.39	13 0.51	7 0.28	6.5 0.26	-	-	
25 0.98	-	M 4	-	-	-	12 0.47	16 0.63	8 0.31	7.5 0.30	-	-	
25 0.98	M 5	M 5	-	M 5	M 5	12 0.47	16 0.63	8 0.31	9.5 0.37	7.5 0.30	-	
25 0.98	-	M 6	-	-	-	12 0.47	16 0.63	8 0.31	9 0.35	-	-	
32 1.26	-	M 4	-	-	-	14 0.55	20 0.79	10 0.39	6.5 0.26	-	-	
32 1.26	-	M 5	-	-	M 5	14 0.55	20 0.79	10 0.39	9.5 0.37	7.5 0.30	-	
32 1.26	M 6	M 6	M 6	M 6	M 6	14 0.55	20 0.79	10 0.39	12 0.47	9 0.35	10.5 0.41	
40 1.57	M 6	M 6	-	M 6	M 6	18 0.71	25 0.98	13 0.51	12 0.47	9 0.35	-	
40 1.57	M 8	M 8	M 8	M 8	M 8	18 0.71	25 0.98	13 0.51	14 0.55	12 0.47	13 0.51	
40 1.57	-	M 10	-	-	-	18 0.71	25 0.98	13 0.51	14 0.55	-	-	
50 1.97	M 8	M 8	M 8	M 8	M 8	22 0.87	32 1.26	17 0.67	14 0.55	12 0.47	16 0.63	
50 1.97	M 10	M 10	M 10	M 10	M 10	22 0.87	32 1.26	17 0.67	18 0.71	15 0.59	16 0.63	
50 1.97	-	M 12	-	-	-	22 0.87	32 1.26	17 0.67	18 0.71	-	-	
63 2.48	M 10	M 10	-	M 10	M 10	26 1.02	40 1.57	21 0.83	18 0.71	15 0.59	-	
63 2.48	M 12	M 12	M 12	M 12	M 12	26 1.02	40 1.57	21 0.83	22 0.87	18 0.71	20 0.79	
63 2.48	-	M 16	-	-	-	26 1.02	40 1.57	21 0.83	22 0.87	-	-	
80 3.15	M 12	M 12	-	M 12	M 12	35 1.38	50 1.97	25 0.98	22 0.87	18 0.71	-	
80 3.15	M 16	M 16	-	M 16	M 16	35 1.38	50 1.97	25 0.98	30 1.18	24 0.94	-	

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

