



3 Type

- E** With tapped blind bore (with cap)
- D** With tapped through bore (without cap)

Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ Type E	2 Type D	d ₃	d ₄	b	h ₁	h ₂	t ₁ min.	t ₂
32 1.26	M 4	-	12 0.47	8 0.31	6 0.24	16.5 0.65	3.5 0.14	6 0.24	-
32 1.26	M 5	M 5	12 0.47	8 0.31	6 0.24	16.5 0.65	3.5 0.14	6 0.24	12 0.47
32 1.26	M 6	M 6	12 0.47	8 0.31	6 0.24	16.5 0.65	3.5 0.14	8 0.31	12 0.47
40 1.57	M 6	-	13.5 0.53	9.5 0.37	6.5 0.26	21 0.83	4.5 0.18	12 0.47	-
40 1.57	M 8	M 8	13.5 0.53	9.5 0.37	6.5 0.26	21 0.83	4.5 0.18	13 0.51	16 0.63

Specification

- Wing body
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black, matte finish
- Tapped insert
Brass
- [Plastic Characteristics](#) → page QVX
- [RoHS compliant](#)

Information

The slightly concave indentations on the ends of the EN 640 small wing nuts help to position the fingers to apply the maximum force when tightening.
Resistant to solvents, oils, grease and other chemical agents.

see also...

- [Wing Nuts EN 634](#) → page QVX
- [Wing Nuts EN 532.1](#) → page QVX
- [Wing Nuts EN 532](#) → page QVX

<p>How to order</p> <p>EN 640-32-M6-E</p>	1	Handle diameter d ₁
	2	Thread d ₂
	3	Type

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

