


Inch | Metric



Inch table

Dimensions in: inches / millimeters					
Length l	d₂ Thread	h₁	h₂	s Square	t min.
2.17 55	1/4 x 20	1.30 33	0.87 22	0.55 14	0.47 12
2.64 67	5/16 x 18	1.46 37	0.98 25	0.63 16	0.63 16
3.15 80	3/8 x 16	1.61 41	1.02 26	0.79 20	0.63 16

Metric table

Dimensions in: millimeters / inches							
Length l	d₁ H7 Bore	d₂ Thread		h₁	h₂	s Square	t min.
55 2.17	B 6	M 6	M 8	33 1.30	22 0.87	14 0.55	12 0.47
67 2.64	B 8	M 8	-	37 1.46	25 0.98	16 0.63	16 0.63
80 3.15	B 8	M 8	M 10	41 1.61	26 1.02	20 0.79	16 0.63

Specification

- Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish
 - Silver, RAL 9006, textured finish
 - Plain, tumbled finish

Flash mark not visible
- SW
 - SR
 - BL

RoHS

Technical Information

ISO Fundamental Tolerances

QVX

T-handles GN 563.2 can be used as either operating handles or for clamping purposes, providing high clamping force.

T-handles are made by forging and therefore they have a structure with high strength and a smooth surface.

Original ELESA design, produced in metal with permission of ELESA S. p. A.

see also...

EN 563 T-Handles (Plastic, Tapped or Blind Bore Type)

EN 563.1 T-Handles (Plastic, with Threaded Stud)

Page

QVX

QVX

How to order (Inch)

1

2

3

GN 563.2-55-1/4X20-BL

1

2

3

Handle length l

Thread d₂

Finish

How to order (Metric)

1

2

3

GN 563.2-67-B8-SR

1

2

3

Handle length l

Bore d₁ (Thread d₂)

Finish