



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂	³ Length l			d ₃	h	k
20 0.79	M 5	10 0.39	16 0.63	-	12 0.47	16 0.63	10 0.39
25 0.98	M 6	16 0.63	20 0.79	30 1.18	16 0.63	19 0.75	11 0.43
32 1.26	M 8	16 0.63	20 0.79	30 1.18	17 0.67	22 0.87	13 0.51

Specification

- Plastic
Technopolymer (Polyamide PA)
- Reinforced
- Temperature resistant to 266 °F (130 °C)
- Black, matte finish
- Threaded stud
Stainless steel AISI 303
- [Stainless Steel Characteristics](#) → page QVX
- [Plastic Characteristics](#) → page QVX
- [RoHS compliant](#)

Information

With their stainless steel threaded stud insert, these EN 591.5 knurled screws are particularly suited to applications where hygienic, climatic and environmental factors require corrosion resistant materials. Resistant to solvents, oils, grease and other chemical agents.

see also...

- [Hollow Knurled Screws GN 421](#) → page QVX
- [Knurled Screws EN 591](#) → page QVX

How to order ¹ ² ³ EN 591.5-20-M5-16	1	Handle diameter d ₁
	2	Thread d ₂
	3	Length l

