

Metric




**elesa**

Original design MPG-C / MPG-T

**SS** Stainless Steel

**1** Type

- T** Retaining profile trapezoidal
- R** Retaining profile round



Metric table

<b>2</b> $d_1$			<b>2</b> $h$	<b>3</b> $d_2$			Dimensions in: millimeters / inches		
Type R			Type T	Retaining rod			EN 6475	EN 6475.1	EN 6475.2
B 10	B 12	B 14	17 0.67	D 12	D 14	D 16	18 / 21	18	20

Specification

**Clamp**

- Plastic, Polyamide (PA)
- Operating temperature  
-22 °F to 212 °F (-30 °C to +100 °C)
- Shock resistant
- Black

**Retaining rod / Socket cap screws / Nuts**

Stainless steel AISI 304

RoHS

Side guide clamps EN 6475.4 attach side guides to conveyor sections. The version with retaining rod additionally requires the use of side guide holders EN 6476, EN 6476.2 or EN 6476.3. The version with an internal thread enables direct mounting, for example on a side wall.

see also...

	Page
EN 6475 Side Guides (Guide Contour Flat)	QVX
EN 6475.1 Side Guides (Guide Contour Rounded)	QVX
EN 6475.2 Side Guides (Guide Contour Flat, Stepped)	QVX
EN 6476 Side Guide Bracket (Rigid, with Contact Edge)	QVX
EN 6476.2 Side Guide Bracket (Swiveling, with Contact Edge)	QVX
EN 6476.3 Side Guide Bracket (Swiveling)	QVX
GN 990 Construction Tubes	QVX

Technical Information

Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order (Without retaining rod)

<b>1</b> Type	<b>2</b> Height h (Diameter $d_1$ )
<b>EN 6475.4-T-17</b>	

How to order (With retaining rod)

<b>1</b> Type	<b>2</b> Diameter $d_1$ (Height h)	<b>3</b> Diameter $d_2$
<b>EN 6475.4-R-B10-D16</b>		

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10