



Inch | Metric

Type A / Type B



elesa

Original design I.281 / I.281+x-SST

SS Stainless Steel

4 Type

- A** With stainless steel threaded spindle
- B** With steel threaded spindle
- E** Without threaded spindle

Inch table

2

3

Dimensions in: inches / millimeters

d ₁	d ₂ 6g Type B	d ₄	d ₅	l ₁	l ₂	l ₃	l ₄	l ₅	A/F Internal hex in mm
0.71 18	1/4 x 20*	0.59 15	0.47 12	1.57 40	0.51 13	0.04 1	1.54 39	1.38 35	4
0.83 21	5/16 x 18*	0.67 17	0.55 14	1.97 50	0.59 15	-	1.97 50	1.69 43	5
0.91 23	5/16 x 18*	0.75 19	0.63 16	2.56 65	0.67 17	0.04 1	2.52 64	2.20 56	6
1.02 26	3/8 x 16*	0.83 21	0.67 17	3.15 80	0.71 18	0.04 1	3.11 79	2.76 70	6
1.10 28	3/8 x 16*	0.87 22	0.75 19	3.54 90	0.71 18	0.04 1	3.50 89	3.11 79	8

* Inch sizes are only available with steel threaded spindle

Metric table

2

3

3

Dimensions in: millimeters / inches

d ₁	d ₂ 6g Type A, Type B	d ₃ ^{+0.3} / _{+0.1} Type E	d ₄	d ₅	l ₁	l ₂	l ₃	l ₄	l ₅	A/F Internal hex
18 0.71	M 6	-	8 0.315	15 0.59	12 0.47	40 1.57	13 0.51	39 1.54	35 1.38	4
21 0.83	M 8	-	10 0.394	17 0.67	14 0.55	50 1.97	15 0.59	50 1.97	43 1.69	5
23 0.91	M 8	-	12 0.472	19 0.75	16 0.63	65 2.56	17 0.67	64 2.52	56 2.20	6
23 0.91	M 10	-	12 0.472	19 0.75	16 0.63	65 2.56	17 0.67	64 2.52	56 2.20	6
26 1.02	M 10	-	13 0.512	21 0.83	17 0.67	80 3.15	18 0.71	79 3.11	70 2.76	6
28 1.10	M 10	-	14 0.551	22 0.87	19 0.75	90 3.54	18 0.71	89 3.50	79 3.11	8
31 1.22	M 12	M 14	16 0.630	25 0.98	20 0.79	102 4.02	20 0.79	100 3.94	89 3.50	8

Specification **1**

Handle

Plastic, Phenolic (PF)

KU

- Operating temperature up to 230 °F (110 °C)
- Black, shiny finish

Threaded spindle

- Type A: Stainless steel AISI 304
- Type B: Steel, matte chrome plated finish

RoHS

Technical Information

Plastic Characteristics QVX

Stainless Steel Characteristics QVX

The outstanding feature of revolving handles EN 598.2 is their highly robust design. They are resistant to solvents, oils, grease and other chemical agents. Type E is suitable for use with user-specific threaded spindles.

How to order (Inch, with threaded spindle)

EN 598.2-KU-18-1/4X20-B

- | | |
|----------|--------------------------------|
| 1 | Material |
| 2 | Handle diameter d ₁ |
| 3 | Thread d ₂ |
| 4 | Type |

How to order (Metric, without threaded spindle)

EN 598.2-KU-26-13-E

- | | |
|----------|--------------------------------|
| 1 | Material |
| 2 | Handle diameter d ₁ |
| 3 | Bore diameter d ₃ |
| 4 | Type |

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

