



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

d₁	Length l						d₂	k
M 3	6 <i>0.24</i>	8 <i>0.31</i>	10 <i>0.39</i>	16 <i>0.63</i>	20 <i>0.79</i>	-	12 <i>0.47</i>	2.5 <i>0.10</i>
M 4	8 <i>0.31</i>	10 <i>0.39</i>	12 <i>0.47</i>	16 <i>0.63</i>	20 <i>0.79</i>	25 <i>0.98</i>	16 <i>0.63</i>	3.5 <i>0.14</i>
M 5	10 <i>0.39</i>	12 <i>0.47</i>	16 <i>0.63</i>	20 <i>0.79</i>	25 <i>0.98</i>	30 <i>1.18</i>	20 <i>0.79</i>	4 <i>0.16</i>
M 6	12 <i>0.47</i>	16 <i>0.63</i>	20 <i>0.79</i>	25 <i>0.98</i>	30 <i>1.18</i>	40 <i>1.57</i>	24 <i>0.94</i>	5 <i>0.20</i>
M 8	16 <i>0.63</i>	20 <i>0.79</i>	25 <i>0.98</i>	30 <i>1.18</i>	35 <i>1.38</i>	40 <i>1.57</i>	30 <i>1.18</i>	6 <i>0.24</i>
M 10	20 <i>0.79</i>	25 <i>0.98</i>	30 <i>1.18</i>	35 <i>1.38</i>	40 <i>1.57</i>	-	36 <i>1.42</i>	8 <i>0.31</i>

Specification

- Steel
 - Property class 5
 - Visible face fine turned
 - Blackened finish **—**
 - Zinc plated, blue passivated finish **ZB**
- Stainless steel AISI 303 **NI**
 - Matte shot-blasted finish
- *Strength Values of Screws* → page 2127
- *Stainless Steel Characteristics* → page 2143
- *RoHS compliant*

Information

DIN 653 knurled thumb screws are turned from solid bar. The thread of the screw extends up to the head and ends in a runout. They can be tightened and loosened quickly without tools.

see also...

- *Knurled Thumb Screws GN 653.10 (Steel, with Brass / Plastic Tip)* → page 707
- *Knurled Thumb Screws GN 653.2 (with Recessed Stud for Loss Protection)* → www.jwwinco.com
- *Knurled Thumb Screws DIN 464 (High Type)* → page 705

On request

- Version in stainless steel (A4 quality)

How to order (Steel, blackened finish)	1 Thread d ₁
DIN 653-M8-35	2 Length l
How to order (Steel, zinc plated)	1 Thread d ₁
DIN 653-M3-8-ZB	2 Length l
	3 Finish
How to order (Stainless steel)	1 Thread d ₁
DIN 653-M5-20-NI	2 Length l
	3 Material