



Metric



SS Stainless Steel

Metric table



Dimensions in: millimeters / inches

d ₁		d ₂	d ₃	l ₁ ≈	l ₂	l ₃	l ₄ ≈	l ₅	l ₆
GN 598.3	GN 598.5								
18 0.71	-	M 5	16 0.63	57 2.24	15 0.59	5 0.20	52 2.05	9.5 0.37	5 0.20
21 0.83	-	M 5	16 0.63	67 2.64	15 0.59	5 0.20	62 2.44	9.5 0.37	5 0.20
22 0.87	-	M 5	16 0.63	73 2.87	15 0.59	5 0.20	68 2.68	9.5 0.37	5 0.20
23 0.91	23 0.91	M 6	20 0.79	87 3.43	19.5 0.77	6 0.24	80 3.15	10.5 0.41	7 0.28
26 1.02	26 1.02	M 6	20 0.79	102 4.02	19.5 0.77	6 0.24	95 3.74	10.5 0.41	7 0.28
28 1.10	28 1.10	M 8	26 1.02	118 4.65	26 1.02	10 0.39	106 4.17	16 0.63	10 0.39

Specification



Handle

- Plastic, Phenolic (PF)
- Operating temperature up to 230 °F (110 °C)
- Black, shiny finish
- Revolving

KU

GN 598.3

Retractable mechanism

Steel, blackened finish

GN 598.5

Retractable mechanism

- Stainless steel
- Stem, retaining pin, AISI 303
- Hub, AISI 316LHC, sintered

RoHS

Technical Information

Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

Retractable handles GN 598.3 / GN 598.5 are suitable when the handle must be withdrawn during automatic operation.

The handle is pulled out of its tapered seat in the direction of the arrow and then tilted. A compression spring locks the handle in both end positions. A positive lock is achieved in the operating position by way of a tapered seat located in the hub of the mechanism.

see also...

Page

GN 798.7 Stepped Safety Retractable Handles (with Steel Mechanism, Automatic Fold-Down Type) QVX

GN 798.8 Stepped Safety Retractable Handles (with Stainless Steel Mechanism, Automatic Fold-Down Type) QVX

How to order (Steel)

GN 598.3-KU-26

- 1 Material
- 2 Handle diameter d₁

How to order (Stainless steel)

GN 598.5-KU-23

- 1 Material
- 2 Handle diameter d₁