


Inch | Metric



elesa
Original design EBK.SOFT



Inch table

Dimensions in: inches / millimeters

¹ d ₁	² d ₂	³ Length l	d ₃	h ₁	h ₂
1.97 50	5/16 x 18	0.75 19	1.42 36	2.52 64	0.79 20
1.97 50	3/8 x 16	0.98 25	1.42 36	2.52 64	0.79 20

Metric table

Dimensions in: millimeters / inches

¹ d ₁	² d ₂	³ Length l	d ₃	h ₁	h ₂
43 1.69	M 6	16 0.63	20 0.79	25 0.98	-
43 1.69	M 8	16 0.63	20 0.79	25 0.98	30 1.18
43 1.69	M 10	20 0.79	25 0.98	30 1.18	50 1.97
50 1.97	M 8	16 0.63	20 0.79	25 0.98	30 1.18
50 1.97	M 10	20 0.79	25 0.98	30 1.18	50 1.97

Specification

Handle

- Base body
Plastic, Polypropylen (PP)
- Softline coating
Thermoplastic elastomer (TPE)
 - Chemically bonded with base body
 - FDA compliant plastic granulate
 - Operating temperature
32 °F to +176 °F (0 °C to +80 °C)
 - Black, matte finish
 - Hardness 70 Shore A

Threaded stud

Steel, zinc plated, blue passivated finish

RoHS

On request

- Revolving ball handles

Technical Information

Product Family Ergostyle®	QVX
Product Family Softline	QVX
Plastic Characteristics	QVX

The Softline coating makes the ball handles EN 675 particularly ergonomic and easy to grip.

The soft, slip-proof contact area improves the grip both in damp (hand perspiration) and in dry ambient conditions, as well as in the event of oily surfaces and in very high or very low temperatures.

The ball handles are suitable for use both as operating elements and for clamping. The „hard“ plastic core guarantees the perfect anchoring of the insert with threaded stud even under heavier clamping or torquing loads.

see also...

	Page
EN 675 Ball Handles (Tapped Insert, without Cover Cap)	QVX
EN 675.1 Ball Handles (Tapped Insert, with Cover Cap)	QVX

How to order (Inch)

¹ ² ³
EN 675-50-5/16X18-19

1	Ball diameter d ₁
2	Thread d ₂
3	Length l

How to order (Metric)

¹ ² ³
EN 675-43-M8-20

1	Ball diameter d ₁
2	Thread d ₂
3	Length l