



4 Type
A Without clamping bolt

Metric table

Dimensions in: millimeters - inches

| 1 d₃ Clamp slot size | 2 l₁ | 3 l₆ | | b | d₂ | h₁ | h₂ min. - max. | l₂ | l₃ | Table slot size |
|-----------------------------------------------------|----------------------------------|----------------------------------|-------------|------------|----------------------|----------------------|-------------------------------------|----------------------|----------------------|-----------------|
| 11 0.43 | 80 3.15 | 39 1.54 | - | 30 1.18 | M 10 | 15 0.59 | 8 - 37 | 15 0.59 | 30 1.18 | 10 |
| 14 0.55 | 100 3.94 | 49 1.93 | 94 3.70 | 40 1.57 | M 12 | 20 0.79 | 10 - 47 10 - 92 | 21 0.83 | 40 1.57 | 12 - 14 |
| 18 0.71 | 125 4.92 | 55 2.17 | 90 3.54 | 50 1.97 | M 16 | 25 0.98 | 13 - 52 13 - 87 | 26 1.02 | 45 1.77 | 16 - 18 |
| 26 1.02 | 200 7.87 | 87 3.43 | 137 5.39 | 70 2.76 | M 26 | 30 1.18 | 20 - 83 20 - 133 | 35 1.38 | 80 3.15 | 24 - 28 |

Specification

- Plain clamp
Tempered steel, lacquer painted finish
- Knurled adjusting screw
Steel
- Hardened
- Property class 8.8
- *Strength Values of Screws → page 2127*
- **RoHS compliant**

Accessory

- T-slot bolts DIN 787 → page 1229
- Fixture nuts DIN 6330 → page 1140
- Heavy duty flat washers DIN 6340 → page 1152

Information

No. 6314 V adjustable plain clamps are particularly suitable for clamping low height workpieces. The clamping height can be adjusted by means of the adjusting screw (knurled or socket head positions).
Adjusting screw included as part of the assembly.

| | | |
|---------------------------------------------------------|----------|--------------------------------------|
| <p>How to order</p> <p>NO. 6314V-18-125-55-A</p> | 1 | Clamp slot size d₃ |
| | 2 | Length l₁ |
| | 3 | Length l₆ |
| | 4 | Type |