



Metric table

Dimensions in: millimeters - inches

d ₁	d ₂	l ₁	l ₂	For threaded ball joint linkages DIN 71802 Size (d ₁)
11.5 <i>0.45</i>	5.5 <i>0.22</i>	4.5 <i>0.18</i>	1.5 <i>0.06</i>	8 <i>0.31</i>
13 <i>0.51</i>	7 <i>0.28</i>	6.5 <i>0.26</i>	3.5 <i>0.14</i>	10 <i>0.39</i>
17 <i>0.67</i>	8.5 <i>0.33</i>	7.5 <i>0.30</i>	3.5 <i>0.14</i>	13 <i>0.51</i>
21 <i>0.83</i>	10.5 <i>0.41</i>	8.5 <i>0.33</i>	4.5 <i>0.18</i>	16 <i>0.63</i>
25 <i>0.98</i>	12.5 <i>0.49</i>	12.5 <i>0.49</i>	7 <i>0.28</i>	19 <i>0.75</i>

Specification

- Rubber (CR)
 - Temperature resistant up to 230 °F (110 °C)
 - Black
- *Elastomer Characteristics* → page 2135
- **RoHS compliant**

On request

- Threaded ball joint linkages with mounted dust cap

Information

GN 710 dust caps prevent dirt from entering in DIN 71802 angled ball joints.

see also...

- *Threaded Ball Joint Linkages DIN 71802 (Steel)* → page 1751
- *Threaded Ball Joint Linkages DIN 71802 (Stainless Steel)* → page 1752

How to order

GN 710-17.5

1 Outside diameter d₁

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10