


Application example



Metric



**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub> g6	<sup>2</sup> h h9	d <sub>2</sub> n6	Length l
6 0.24	2.5 0.10	4 0.16	6.5 0.26
6 0.24	4.5 0.18	4 0.16	8.5 0.33
6 0.24	5 0.20	4 0.16	6 0.24
10 0.39	4.5 0.18	6 0.24	8.5 0.33
10 0.39	8 0.31	6 0.24	8 0.31
16 0.63	5 0.20	8 0.31	10 0.39
16 0.63	13 0.51	8 0.31	10 0.39
20 0.79	6 0.24	10 0.39	12 0.47
20 0.79	12 0.47	10 0.39	12 0.47
25 0.98	8 0.31	12 0.47	14 0.55
25 0.98	20 0.79	12 0.47	14 0.55
25 0.98	30 1.18	12 0.47	14 0.55
30 1.18	25 0.98	16 0.63	20 0.79
30 1.18	40 1.57	16 0.63	20 0.79
30 1.18	50 1.97	16 0.63	20 0.79
30 1.18	65 2.56	16 0.63	20 0.79
40 1.57	13 0.51	20 0.79	20 0.79
40 1.57	32 1.26	20 0.79	20 0.79

**Specification**

- Steel, hardened
- ISO Fundamental Tolerances → page 2129
- RoHS compliant

**Information**

- GN 6321.1 seating pins can also be used as stops or feet.
- see also...
- Locating / Seating Pins DIN 6321 → page 1178

How to order

**GN 6321.1-25-8**

- <sup>1</sup> Diameter d<sub>1</sub>
- <sup>2</sup> Height h