


Metric



elesa
Original design I.222

Metric table

Dimensions in: millimeters / inches

¹ d_1	² d_2		d_3	h	t_1 min.	$t_2 \pm 0.5$
15 0.59	M 6	-	12 0.47	25 0.98	16 0.63	3.5 0.14
20 0.79	M 8	-	14 0.55	31 1.22	20 0.79	3.5 0.14
26 1.02	M 8	M 10	17 0.67	42 1.65	20 0.79	5 0.20
33 1.30	M 10	M 12	20 0.79	54 2.13	40 1.57	8 0.31
38 1.50	M 12	-	23 0.91	68 2.68	45 1.77	11 0.43
41 1.61	M 14	M 16	25 0.98	87 3.43	55 2.17	14 0.55

Specification

- Plastic**, Phenolic (PF)
- Operating temperature
-4 °F to 230 °F (-20 °C to +110 °C)
 - Black, shiny finish

RoHS

Domed gear lever knobs EN 719 are very often used in place of ball knobs DIN 319 on switch levers, gear levers etc. Knobs for such applications are often chosen for ergonomic reasons.

see also...

	Page
EN 719.1 Domed Gear Lever Knobs (Press-On Type)	QVX
EN 719.2 Domed Gear Lever Knobs (Tapped or Press-On Type)	QVX

Technical Information

Plastic Characteristics	QVX
-------------------------	-----

How to order

EN 719-20-M8

- 1 Handle diameter d_1
- 2 Thread d_2

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

