



- 3 Type**
- A With friction ring
 - B Without friction ring

Metric table

Dimensions in: millimeters - inches

d₀ Knob Ø GN 723.4	d₁	d₂ H8 Bore		d₃ -0.1	d₄	k	l₁	l₂
27 1.06	33.5 1.32	B 6	-	23.3 .92	3.4 .13	13 .51	11.2 .44	4 .16
34 1.34	41 1.61	B 6	B 8	29.3 1.15	3.4 .13	18 .71	14.2 .56	5 .20
42 1.65	50 1.97	B 8	B 10	37.3 1.47	4.5 .18	24 .94	16.2 .64	5 .20

Specification

- Aluminum
Black, anodized finish
- Reference arrow
White, laser engraved
- Clamp ring
NBR synthetic rubber
- Friction ring
Technopolymer (Polyamide)
- ISO Fundamental Tolerances → page QVX
- RoHS compliant

Information

GN 723.3 control knob flanges are used together with GN 723.4 knurled control knobs, which offer the following advantages:

- They have a reference mark to line up with the control knob scale.
- They give additional support to the control shaft.
- They can be fitted with end stop pins to limit the angular movement of the control knob (the introduction of rest positions with the aid of ball plungers is also possible).
- The version with friction ring prevents unexpected movement due to vibration.

see also...

- Knurled Control Knobs GN 723.4 (Aluminum) → page QVX

How to order GN 723.3-50-B8-A	1	Outside diameter d₁
	2	Bore d₂
	3	Type