



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂	Length l ≈								d ₃	h ₁	h ₂	h ₃
32 1.26	M 6	16 0.63	20 0.79	25 0.98	30 1.18	35 1.38	45 1.77	-	-	12 0.47	20 0.79	10 0.39	9 0.35
40 1.57	M 8	16 0.63	20 0.79	25 0.98	30 1.18	35 1.38	40 1.57	45 1.77	55 2.17	14 0.55	25 0.98	13 0.51	10 0.39
50 1.97	M 10	25 0.98	30 1.18	35 1.38	45 1.77	55 2.17	-	-	-	18 0.71	32 1.26	20 0.79	12 0.47
63 2.48	M 12	30 1.18	35 1.38	40 1.57	50 1.97	60 2.36	-	-	-	20 0.79	40 1.57	25 0.98	14 0.55

Specification

- Hand knob
Plastic
Technopolymer (Polyamide PA)
- Shock-resistant
- Black, matte finish
- **GN 6335.4**
Threaded stud
Steel, zinc plated, blue passivated finish
- **GN 6335.5**
Threaded stud
Stainless steel AISI 303
- *Plastic Characteristics* → page 2135
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

1

TE

Information

GN 6335.4 and GN 6335.5 hand knobs with protruding hub and threaded stud increase the range of application.
Due to the protruding hub and threaded stud being a solid one-piece unit, a strong and secure contact to the clamping surface is created.
see also...
• *Hand Knobs GN 6335.4 (without Protruding Hub, with Steel Threaded Stud)* → page 634
• *Hand Knobs GN 6335.5 (without Protruding Hub, with Stainless Steel Threaded Stud)* → page 634

On request

- Special shorter than listed stud lengths and various stud tips

How to order (Steel threaded stud)	1 Material
GN 6335.4-TE-32-M6-25	2 Handle diameter d ₁
	3 Thread d ₂
	4 Length l
How to order (Stainless steel threaded stud)	1 Material
GN 6335.5-TE-63-M12-60	2 Handle diameter d ₁
	3 Thread d ₂
	4 Length l

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4