




Metric table

Dimensions in: millimeters / inches											
d ₁	d ₂ H8		b	d ₃	d ₄	d ₅	l ₁	l ₂	t ₁ min.	t ₂ +0.2	s ^{+0.3} / _{+0.1}
34 1.34	B 6	B 8	28 1.10	M 5	6 0.24	20 0.79	20 0.79	7.5 0.30	14 0.55	4 0.157	4 0.157
42 1.65	B 8	B 10	35 1.38	M 5	6 0.24	30 1.18	22 0.87	7.5 0.30	16 0.63	4 0.157	4 0.157

Specification

Knob	Control knobs GN 729 are usually selected for applications which require a limited movement within 180°.
Aluminum	By using limiting pins which protrude in the circular groove, the angle of rotation can be restricted.
• Black, anodized finish	The bore (d ₄) is for a ball plunger, like the GN 614 series, and acts as a simple detent.
• Indexing line	
- White	
- Laser engraved	
Set screw DIN 916	Technical Information
Stainless steel	ISO Fundamental Tolerances
With internal hex and serrated point	
RoHS	Accessory
	GN 826 Control Knob Flanges (for Adjustable Spindles)