



SS Stainless Steel

4 Type

- D** With tapped through bore
- E** With tapped blind bore

Metric table

Dimensions in: millimeters - inches

2 d_1	3 d_2	d_3	h_1	h_2	t_1 min.	t_2
32 1.26	M 6	12 0.47	20 0.79	9 0.35	12 0.47	10 0.39
40 1.57	M 8	14 0.55	25 0.98	13 0.51	15 0.59	13 0.51
50 1.97	M 10	18 0.71	32 1.26	18 0.71	18 0.71	16 0.63
63 2.48	M 12	20 0.79	40 1.57	23 0.91	22 0.87	20 0.79

Specification

- Stainless steel precision casting AISI 316 Polished finish **A4 PL**
- *Stainless Steel Characteristics* → page QVX
- RoHS compliant

Information

Hand knobs GN 6335 satisfy the dimensions of the DIN 6335 but differ in terms of their non-scooping geometry, which makes cleaning easier and helps prevent possible build-up of dirt.

They are suitable for areas with special hygienic requirements and, thanks to the material used, for applications in highly corrosive environments.

see also...

- *Hand Knobs DIN 6335 (Plastic)* → page QVX
- *Hand Knobs DIN 6335 (Cast Iron / Stainless Steel / Aluminum)* → page QVX
- *Hand Knobs GN 6335.1 (Phenolic Plastic, with Protruding Hub)* → page QVX
- *Hand Knobs GN 6335.2 (Technopolymer Plastic, with Protruding Hub)* → page QVX

How to order

GN 6335-A4-40-M8-E-PL

1	Material
2	Handle diameter d_1
3	Thread d_2
4	Type
5	Finish