



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

² d ₁	³ d ₂	⁴ Length l ≈								d ₃	h ₁	h ₂	h ₃
25 0.98	M 5	10 0.39	15 0.59	20 0.79	-	-	-	-	-	10 0.39	16 0.63	8 0.31	6 0.24
32 1.26	M 6	16 0.63	20 0.79	25 0.98	30 1.18	35 1.38	45 1.77	-	-	12 0.47	20 0.79	10 0.39	8.5 0.33
40 1.57	M 8	16 0.63	20 0.79	25 0.98	30 1.18	35 1.38	40 1.57	45 1.77	55 2.17	14 0.55	26 1.02	13 0.51	10 0.39
50 1.97	M 10	25 0.98	30 1.18	35 1.38	45 1.77	55 2.17	-	-	-	18 0.71	32 1.26	17 0.67	10 0.39
63 2.48	M 12	30 1.18	35 1.38	40 1.57	50 1.97	60 2.36	-	-	-	20 0.79	40 1.57	21 0.83	14 0.55

Specification

- Star knob
Plastic
Technopolymer (Polyamide PA)
- Shock-resistant
- Black, matte finish

¹

TE

- **GN 6336.4**
Threaded stud
Steel, zinc plated, blue passivated finish

- **GN 6336.5**
Threaded stud
Stainless steel AISI 303

- *Plastic Characteristics* → page 2135
- *Stainless Steel Characteristics* → page 2143
- *RoHS compliant*

On request

- Special shorter than listed stud lengths and various stud tips

Information

GN 6336.4 star knobs with protruding hub and threaded stud increase the range of application. Due to the protruding hub and threaded stud being a solid one-piece unit, a strong and secure contact to the clamping surface is created.

see also...

- *Star Knobs GN 6336.4 (without Protruding Hub, with Steel Threaded Stud)* → page 578
- *Star Knobs GN 6336.5 (without Protruding Hub, with Stainless Steel Threaded Stud)* → page 578

How to order (Steel threaded stud)	¹ Material
² GN 6336.4-TE-50-M10-30	² Handle diameter d ₁
	³ Thread d ₂
	⁴ Length l

How to order (Stainless steel threaded stud)	¹ Material
² GN 6336.5-TE-40-M8-16	² Handle diameter d ₁
	³ Thread d ₂
	⁴ Length l

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4