



Metric



3 Type

- L** Angled lever with plain bore
- N** Angled lever with tapped bore

Metric table

Dimensions in: millimeters / inches

1 l_1	2 d_1 Thread	2 d_2 H7 Bore	b	d_3	d_4	d_5	d_6	$h \approx$	$l_2 \approx$
63 2.48	M 8	B 8	12 0.47	16 0.63	12.5 0.49	20 0.79	8 0.31	33 1.30	60 2.36
80 3.15	M 10	B 10	14.5 0.57	20 0.79	16 0.63	20 0.79	9 0.35	40 1.57	76 2.99
100 3.94	M 12	B 12	18.5 0.73	25 0.98	20 0.79	25 0.98	11 0.43	50 1.97	95 3.74
125 4.92	M 16	B 16	24 0.94	32 1.26	25 0.98	32 1.26	15 0.59	63 2.48	119 4.69
160 6.30	M 20	B 20	30 1.18	40 1.57	31 1.22	40 1.57	18 0.71	80 3.15	152 5.98

Specification

Hub / Shaft

Steel, blackened finish
Turned

Ball knob DIN 319

Plastic, Phenolic (PF)
Black, shiny finish

RoHS

On request

Special inch or metric size bores and threads

Ball levers DIN 6337 have the same ball diameter d_1 and length l_1 as clamping levers DIN 99.

see also...

	Page
GN 6337.3 Adjustable Ball Levers	QVX
DIN 99 Clamping Levers	QVX
GN 212 Tension Levers	QVX

Technical Information

ISO Fundamental Tolerances	QVX
----------------------------	-----

How to order

DIN 6337-100-M12-N

1	Lever length l_1
2	Thread d_1 (Bore d_2)
3	Type

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

