



Metric



elesa

Original design ETH-EP/-AN



IF product design award



reddot design award winner

Metric table

1		2		3															
d ₁	l ₁ ±1					a	b	d ₂	h ₁	h ₂	h ₃	l ₂	l ₃	l ₄					
28	300	400	500	600	700	-	62.5	28	10.5	54	68	20	26	19.5	20.3				
1.10	11.81	15.75	19.69	23.62	27.56		2.46	1.10	0.41	2.13	2.68	0.79	1.02	0.77	0.80				
35	300	400	500	600	700	1000	74	35	10.5	67.5	85	28	24.5	28.5	18.5				
1.38	11.81	15.75	19.69	23.62	27.56	39.37	2.91	1.38	0.41	2.66	3.35	1.10	0.96	1.12	0.73				

Dimensions in: millimeters / inches

Specification

Handle tube

Aluminum, wall thickness 2 mm

EN 767

Tube

Powder coated

Graphite black, metal effect, matte finish

EN 767.1

Tube

Anodized finish, natural color

End caps

Plastic, Polyamide (PA)

- Black-gray, RAL 7021, shiny finish
- Orange, RAL 2004, shiny finish
- Gray, RAL 7035, shiny finish
- Yellow, RAL 1021, shiny finish
- Blue, RAL 5024, shiny finish
- Red, RAL 3000, shiny finish
- Green, RAL 6017, shiny finish

- **DSG**
- **DOR**
- **DGR**
- **DGB**
- **DBL**
- **DRT**
- **DGN**

End pieces

Plastic, Polyamide (PA)

- Glass fiber reinforced
- Operating temperature -4 °F to +212 °F (-20 °C to +100 °C)
- Black-gray, matte finish, similar to RAL 7021

RoHS

On request

- Tube, end pieces and end caps in white (WS)

Tubular handles EN 767 / EN 767.2 are highly resistant to wear, scratches and chemical agents. Avoid continuous and prolonged contact with boiling water or steam. Handle legs resistant to solvents, oils, greases and other chemical agents.

Special expansion-assembly system between tube and handle legs prevents rotation during operations. The mechanisms (screws / nuts / clamps) are shrouded by the removable end caps. On assembly the two end caps are inserted from above. To remove the end caps, a flat screw driver should be inserted in the provided recess to pry them out of their location. End caps are available in the different Ergostyle® colors which offers additional possibilities for a variety of color schemes.

see also...

GN 667 Tubular Grip Handles (Mounting from the Operator's Side) QVX

Technical Information

Product Family Ergostyle® QVX

Strength Values QVX

Load Capacity Information QVX

Plastic Characteristics QVX

How to order (Powder coated tube)	1	Handle diameter d ₁
	2	Length l ₁
EN 767-28-300-DSG	3	Color of the end cap

How to order (Anodized tube)	1	Handle diameter d ₁
	2	Length l ₁
EN 767.1-28-300-DSG	3	Color of the end cap

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

