




1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

Metric



SS Stainless Steel

Metric table

Dimensions in: millimeters / inches

d <sub>1</sub>		d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub> ≈	l <sub>4</sub>	s
KT	NI								
16 0.63	-	M 6	10 0.39	13 0.51	41.5 1.63	12 0.47	4 0.16	15 0.59	8 0.31
18 0.71	18 0.71	M 6	10 0.39	14.5 0.57	56 2.20	13 0.51	4 0.16	19 0.75	8 0.31
22 0.87	22 0.87	M 8	14 0.55	18.5 0.73	59 2.32	14 0.55	5.2 0.20	21 0.83	11 0.43
24 0.94	24 0.94	M 10	14 0.55	18.5 0.73	74 2.91	16 0.63	5.2 0.20	27 1.06	11 0.43
25 0.98	-	M 10	16 0.63	20 0.79	84 3.31	16 0.63	5.5 0.22	30 1.18	13 0.51

Specification

Handle

- Plastic, Polyamide (PA) **KT**
- Operating temperature up to 194 °F (90 °C)
- Black, matte finish
- Stainless steel AISI 303 **NI**
- Fine turned

Threaded spindle

Stainless steel AISI 303

RoHS

Stepped cylindrical revolving handles GN 798.4 are noted for their modern design, and the stepped shape provides the operator with a better grip.

see also...

**GN 798.5** Stepped Retractable Handles (with Locking Mechanism) **QVX**

Technical Information

Plastic Characteristics **QVX**

Stainless Steel Characteristics **QVX**

How to order

**GN 798.4-KT-16-M6**

- 1 Material
- 2 Handle diameter d<sub>1</sub>
- 3 Thread d<sub>2</sub>