



Metric table



Dimensions in: millimeters - inches

| d ₁ | d ₂ | s | For screws with thread size |
|----------------|----------------|------------|-----------------------------|
| 6.4 0.25 | 17 0.67 | 3 0.12 | M 6 |
| 8.4 0.33 | 23 0.91 | 4 0.16 | M 8 |
| 10.5 0.41 | 28 1.10 | 4 0.16 | M 10 |
| 13 0.51 | 35 1.38 | 5 0.20 | M 12 |
| 15 0.59 | 40 1.57 | 5 0.20 | M 14 |
| 17 0.67 | 45 1.77 | 6 0.24 | M 16 |
| 19 0.75 | 45 1.77 | 6 0.24 | M 18 |
| 21 0.83 | 50 1.97 | 6 0.24 | M 20 |
| 23 0.91 | 50 1.97 | 6 0.24 | M 22 |
| 25 0.98 | 60 2.36 | 8 0.31 | M 24 |
| 28 1.10 | 68 2.68 | 10 0.39 | M 27 |
| 31 1.22 | 68 2.68 | 10 0.39 | M 30 |
| 38 1.50 | 80 3.15 | 10 0.39 | M 36 |
| 44 1.73 | 100 3.94 | 15 0.59 | M 42 |
| 50 1.97 | 108 4.25 | 17 0.67 | M 48 |

Specification

- Heat-treated steel
 - Tempered
 - Hardness (350 + 80) HV 30
 - Phosphate-treated
 - Punched, not deburred
- RoHS compliant

Information

DIN 6340 heavy duty washers are mainly used for elongated holes.

see also...

- Heavy Duty Washers GN 6339 → page 1148

How to order

DIN 6340-17

1 Inner diameter d₁