



Flat shoulder screw DIN 923



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² b	d ₂	d ₃	l ₁	l ₂	l ₃	l ₄	s - 0.5	Screw thread DIN 923
38 1.50	7.5 0.30	9 0.35	6 0.24	19.6 0.77	11 0.43	29 1.14	19 0.75	9.8 0.39	M 6 x 10
43 1.69	9.5 0.37	9 0.35	8 0.31	21.6 0.85	14 0.55	32.5 1.28	21 0.83	9.8 0.39	M 6 x 10
48 1.89	11.5 0.45	9 0.35	10 0.39	23.6 0.93	17 0.67	36.5 1.44	23 0.91	9.8 0.39	M 6 x 10
61 2.40	13.5 0.53	11 0.43	12 0.47	29.6 1.17	22 0.87	45 1.77	29 1.14	11.8 0.46	M 8 x 12
68 2.68	17.5 0.69	11 0.43	16 0.63	33.6 1.32	25 0.98	50 1.97	33 1.30	11.8 0.46	M 8 x 12
74 2.91	21.5 0.85	11 0.43	20 0.79	36.6 1.44	28 1.10	55 2.17	36 1.42	11.8 0.46	M 8 x 12
82 3.23	25.5 1.00	11 0.43	24 0.94	40.6 1.60	32 1.26	62 2.44	40 1.57	15.8 0.62	M 8 x 16
97 3.82	32 1.26	11 0.43	30 1.18	49 1.93	39 1.54	73 2.87	48 1.89	15.8 0.62	M 8 x 16

Specification

- Washer
Steel
- Tempered
- Blackened finish
- Flat shoulder screw DIN 923
Steel, blackened finish
- RoHS compliant

Information

DIN 6371 swing C-washers transfer the clamping force of a screw or nut to the workpiece. They are hinged and thus can be swung out of the clamping point after releasing the screw thread.
DIN 923 flat shoulder screws are included.

How to order	
¹	Outer diameter d ₁
²	Inner diameter b

DIN 6371-48-11.5