




Metric table

1

2

Dimensions in: millimeters / inches																
l_1	d	h_1	h_2	h_3	h_4	h_5	l_2	l_3	l_4	l_5	$m_1 \pm 0.1$	$m_2 \pm 0.1$	m_3	m_4	s	
90 3.54	4.2 0.17	29 1.14	16.5 0.65	47 1.85	77 3.03	16 0.63	141 5.55	96 3.78	135 5.31	65 2.56	118 4.646	79 3.110	16 0.63	3 0.12	3 0.12	
105 4.13	5.2 0.20	43 1.69	17 0.67	60 2.36	95 3.74	18 0.71	167 6.57	116 4.57	158 6.22	86 3.39	141 5.551	98 3.858	15 0.59	4.5 0.18	3 0.12	

Specification

2

Handle

Plastic, Polyamide (PA)

- Glass fiber reinforced
- Operating temperature

-22 °F to +212 °F (-30 °C to +100 °C)

Colors

- Black, RAL 9005, matte finish

- Gray, RAL 7035, matte finish

- White, RAL 9002, matte finish

● SW

● GR

○ WS

Pin

Stainless steel AISI 303

Return springs

Stainless steel AISI 302

RoHS

On request

Various metric size fasteners and kit packaging

Folding handles EN 825.2 with recessed tray are used if the handle is to protrude by a maximum of 3 mm when folded down. After releasing the handle, it returns to its starting position by spring-loaded return.

see also...

GN 425.8 Folding Handles with Recessed Tray (with Handle Held or Spring Return)

EN 825.1 Folding Handles (Plastic, with Spring-Loaded Return)

Page

QVX

QVX

Technical Information

Installation Dimensions

Strength Values

Plastic Characteristics

Stainless Steel Characteristics

QVX

QVX

QVX


QVX

How to order	1	Length l_1
	2	Color



Folding Handle with Recessed Tray EN 825.2
Folding Handle EN 825.1 → page QVX

Installation Dimensions



for l ₁ = 90 mm					for l ₁ = 105 mm				
d	x +0.2	y +0.2	m ₁ ±0.1	m ₂ ±0.1	d	x -0.2	y -0.2	m ₁ ±0.1	m ₂ ±0.1
M4	135 5.315	65 2.559	118 4.646	79 3.110	M 5	158 6.221	86 3.386	141 5.551	98 3.858

