



Inch | Metric



elesa
Original design EKK.p



Inch table

Dimensions in: inches / millimeters

¹ d ₁	² d ₂	³ Length l	d ₃	h ₁	h ₂
0.83 21	10 x 32	0.75 19	0.49 12.5	0.71 18	0.41 10.5
0.98 25	1/4 x 20	0.75 19	0.57 14.5	0.89 22.5	0.55 14
1.22 31	5/16 x 18	0.75 19	0.73 18.5	1.06 27	0.67 17

Metric table

Dimensions in: millimeters / inches

¹ d ₁	² d ₂	³ Length l	d ₃	h ₁	h ₂			
16 0.63	M 3	10 0.39	16 0.63	-	-	8.5 0.33	13 0.51	8.5 0.33
18 0.71	M 4	10 0.39	16 0.63	-	-	10.5 0.41	15.5 0.61	10.5 0.41
21 0.83	M 5	10 0.39	16 0.63	20 0.79	-	12.5 0.49	18 0.71	10.5 0.41
21 0.83	M 6	16 0.63	20 0.79	30 1.18	-	12.5 0.49	18 0.71	10.5 0.41
25 0.98	M 6	16 0.63	20 0.79	25 0.98	30 1.18	14.5 0.57	22.5 0.89	14 0.55
25 0.98	M 8	20 0.79	25 0.98	30 1.18	40 1.57	14.5 0.57	22.5 0.89	14 0.55
31 1.22	M 8	20 0.79	25 0.98	30 1.18	40 1.57	18.5 0.73	27 1.06	17 0.67
31 1.22	M 10	30 1.18	40 1.57	-	-	18.5 0.73	27 1.06	17 0.67

Specification ⁴

Knob

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature
-22 °F to +266 °F (-30 °C to +130 °C)
- Black-gray, RAL 7021, matte finish ● **SG**

Threaded stud

Steel, zinc plated, blue passivated finish

RoHS

When used as a push-pull button, the thumb rests naturally on the concave front surface, making it easier to grip the knurled knob EN 676. The slight knurling on the rim of the knob makes tightening or clamping operations easier.

Resistant to solvents, oils, grease and other chemical agents.

see also...

	Page
EN 676 Knurled Knobs (Plastic, with Brass Tapped Insert)	QVX
GN 76 Mushroom Shaped Knobs (Plastic)	QVX

Technical Information

Product Family Ergostyle®	QVX
Plastic Characteristics	QVX

How to order (Inch)

¹ ² ³ ⁴
EN 676-21-10X32-19-SG

- | | |
|---|--------------------------------|
| 1 | Handle diameter d ₁ |
| 2 | Thread d ₂ |
| 3 | Stud length l |
| 4 | Color |

How to order (Metric)

¹ ² ³ ⁴
EN 676-31-M8-25-SG

- | | |
|---|--------------------------------|
| 1 | Handle diameter d ₁ |
| 2 | Thread d ₂ |
| 3 | Stud length l |
| 4 | Color |

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

