


Metric



4 Type

A Both ends rounded

Metric table

1 2 3

Dimensions in: millimeters / inches

b h9	h		Length l																For shaft Ø from ... to	
2 0.079	2 0.08	6 0.24	8 0.31	10 0.39	12 0.47	14 0.55	16 0.63	18 0.71	20 0.79	-	-	-	-	-	-	-	-	-	-	6...8
3 0.118	3 0.12	6 0.24	8 0.31	10 0.39	12 0.47	14 0.55	16 0.63	18 0.71	20 0.79	22 0.87	25 0.98	28 1.10	30 1.18	32 1.26	35 1.38	36 1.42	-	-	-	8...10
4 0.157	4 0.16	6 0.24	8 0.31	10 0.39	12 0.47	14 0.55	16 0.63	18 0.71	20 0.79	22 0.87	25 0.98	28 1.10	32 1.26	36 1.42	40 1.57	45 1.77	45	-	-	10...12
5 0.197	5 0.20	8 0.31	10 0.39	12 0.47	14 0.55	16 0.63	18 0.71	20 0.79	22 0.87	25 0.98	28 1.10	32 1.26	36 1.42	40 1.57	45 1.77	50 1.97	-	-	-	12...17
6 0.236	6 0.24	12 0.47	14 0.55	16 0.63	18 0.71	20 0.79	22 0.87	25 0.98	28 1.10	32 1.26	36 1.42	40 1.57	45 1.77	50 1.97	56 2.20	63 2.48	-	-	-	17...22
8 0.315	7 0.28	12 0.47	14 0.55	16 0.63	18 0.71	20 0.79	22 0.87	25 0.98	28 1.10	32 1.26	36 1.42	40 1.57	45 1.77	50 1.97	56 2.20	63 2.48	70 2.76	80 3.15	90 3.54	22...30
10 0.394	8 0.31	16 0.63	18 0.71	20 0.79	22 0.87	25 0.98	28 1.10	32 1.26	36 1.42	40 1.57	45 1.77	50 1.97	56 2.20	63 2.48	70 2.76	80 3.15	90 3.54	100 3.94	110 4.33	30...38
12 0.472	8 0.31	20 0.79	25 0.98	28 1.10	32 1.26	36 1.42	40 1.57	45 1.77	50 1.97	56 2.20	63 2.48	70 2.76	80 3.15	90 3.54	100 3.94	125 4.92	-	-	-	38...44

Specification

Steel C45

Plain finish

RoHS

On request

b = 14, 16, 18, 20 mm

see also...

DIN 6885 Parallel Keys (Stainless Steel)

Page

QVX

Technical Information

Keyways WN 6885 / DIN 6885-1 (High Type)

Keyways DIN 6885-2 (Low Type)

ISO Fundamental Tolerances

QVX

QVX

QVX

How to order

DIN 6885-6-6-28-A

- 1 Width b
- 2 Height h
- 3 Length l
- 4 Type

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10