



Stainless Steel



IF product design award



GERMAN DESIGN AWARD

Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂	b	d ₃	h ₁	h ₂ ≈	t min.
32 1.26	M 5	4 0.16	9 0.35	18 0.71	3 0.12	8 0.31
32 1.26	M 6	4 0.16	9 0.35	18 0.71	3 0.12	9 0.35
40 1.57	M 6	4 0.16	11 0.43	21 0.83	3 0.12	9 0.35
40 1.57	M 8	4 0.16	11 0.43	21 0.83	3 0.12	12 0.47
50 1.97	M 8	6 0.24	13 0.51	26 1.02	3 0.12	12 0.47
50 1.97	M 10	6 0.24	13 0.51	26 1.02	3 0.12	15 0.59
63 2.48	M 10	11 0.43	16 0.63	33 1.30	4 0.16	15 0.59
63 2.48	M 12	11 0.43	16 0.63	33 1.30	4 0.16	18 0.71

Specification

Stainless steel
precision casting AISI 316
- Matte shot-blasted finish
- Polished finish



MT
PL

- [Stainless Steel Characteristics](#) → page 2143
- [RoHS compliant](#)

Information

Wing nuts GN 8340 clamp and fasten parts easily without tools. The ergonomic shape allows for high tightening forces.

The wing nuts can also be used in particularly aggressive environments thanks to the material used.

see also...

- [Wing Nuts GN 8341 \(Stainless Steel, Hygienic Design\)](#) → page XYZ
- [Wing Screws GN 8350 \(Stainless Steel\)](#) → page XYZ
- [Wing Nuts GN 432 \(Stainless Steel\)](#) → page XYZ
- [Wing Nuts GN 434 \(Stainless Steel\)](#) → page XYZ
- [Wing Nuts GN 834 \(Stainless Steel\)](#) → page XYZ
- [T-Handles GN 5063 \(Stainless Steel\)](#) → page XYZ

How to order

¹ ² ³
GN 8340-32-M5-MT

- ¹ Handle diameter d₁
- ² Thread d₂
- ³ Finish