



**3 Type**

- A** With screw-on flange
- B** With internal thread
- C** With external thread

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> d	<b>2</b> r	b	$l_1 \approx$	$l_2$	$l_3$ min.	$l_4$
17 0.67	40 1.57	10 0.39	5.5 0.22	16.5 0.65	21.5 0.85	11 0.43
17 0.67	55 2.17	10 0.39	5.5 0.22	16.5 0.65	21.5 0.85	11 0.43

**Specification**

- Latch arm  
Zinc die-cast  
Powder coated  
Black, RAL 9005, textured finish ● **SW**  
Red, RAL 3000, textured finish ● **RS**
- Indexing mechanism  
- Type A  
Zinc die-cast / plastic  
- Type B, C  
Steel / plastic  
Steel parts zinc plated, blue passivated finish
- Screw-on flange  
Zinc die-cast  
Powder coated  
Black, matte finish
- RoHS compliant

**Information**

GN 702 stop latches offer a fast and easy way to close and hold doors, flaps, slide-in modules, etc. They latch in four positions (90°).

Type C stop latches have the same connecting dimensions as GN 115.1 and GN 115.6 mini latches. The mounting bores are to be selected accordingly.

The installation bore in the door leaf is usually generated by punching or laser machining during a mass production run.

For small production runs and steel sheets below 2 mm thickness, GN 123 sheet metal punches are the tool of choice. → [www.jwwinco.com](http://www.jwwinco.com)

The installation bore holes can also be created by drilling or milling.

How to order	
<b>1</b>	Handle diameter d
<b>2</b>	Radius r
<b>3</b>	Type
<b>4</b>	Color

**GN 702-17-40-C-SW**