


Metric



SS Stainless Steel



3 Type

W Figures horizontally arranged (Figure sequences L, M, R)

S Figures vertically arranged (Figure sequences U, M, O)

GN 711.1

Application example



Metric table

2

Dimensions in: millimeters / inches

Length I (Scale)									
50	100	150	200	300	400	500	750*	1000*	
1.97	3.94	5.91	7.87	11.81	15.75	19.69	29.53	39.37	

* The NI-version of this length consists of 2 parts

Specification

Stainless steel

- Thickness 0.6 mm
- Scale etched

1

NI

Plastic

- Thickness 0.3 mm
- Highlighted in silver
- Scale printed

KUS

RoHS

Rulers GN 711 are a convenient measuring device for such applications where consistency, repeatability and accuracy measuring various lengths and heights in either a vertical or horizontal position is important.

The position of linear actuator connectors can be easily read from rulers GN 711. With reference arrows GN 711.1, reference points can be marked on rulers or reference positions in machines.

To apply the ruler, remove the protective strip on the back and affix to a clean and dry surface. The engraved side of the stainless steel version is also protected by a strip of plastic film.

Indicator arrows GN 711.1 for rulers are to be ordered separately.

see also...

Page

GN 711.2 Rulers (Aluminum, with Mounting Holes)

QVX

GN 711.3 Indicator Arrows (Aluminum, with Mounting Holes)

QVX

How to order (Ruler)

GN 711-NI-100-W-L

- 1** Material
- 2** Length I (Scale)
- 3** Type
- 4** Figure sequences

How to order (Indicator arrow)

GN 711.1-KUS

- 1** Material

