



**3 Type**

- A With bore for socket cap screw
- B With mounting thread  $d_2$

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> <b>b</b> Size of the slide	<b>2</b> <b>l<sub>1</sub></b>	<b>d<sub>1</sub></b> For socket cap screws DIN 912	<b>d<sub>2</sub></b>	<b>h</b>	<b>l<sub>2</sub></b>	<b>l<sub>3</sub></b>	<b>l<sub>4</sub></b>	<b>l<sub>5</sub></b>
30 1.18	41 1.61	2.7 0.11	M 2.5	4.2 0.17	35.4 1.39	41 1.61	35.4 1.39	6.5 0.26
50 1.97	67 2.64	3.3 0.13	M 3	7 0.28	58 2.28	67 2.64	58 2.28	10 0.39
80 3.15	105 4.13	4.5 0.18	M 4	12.5 0.49	92 3.62	105 4.13	92 3.62	14.5 0.57
120 4.72	145 5.71	5.5 0.22	M 5	13.8 0.54	131.8 5.19	145 5.71	131.8 5.19	14.5 0.57

**Specification**

- Body  
Aluminum  
Anodized finish, natural color
- Socket cap screws DIN 912  
Stainless steel
- RoHS compliant

**Information**

GN 900.1 fastening units are used to mount GN 900 adjustable slide units on the machine side. The mounting is made on the outside ledge of the slide so that the inner side can still be moved within a limited range.

A fastening unit consists of two mounting rails and four socket cap screws, which are included.

see also...  
• *Adjustable Slide Units GN 900* → page 1942

<b>How to order</b> <b>GN900.1-80-105-A</b>	<b>1</b>	Width <b>b</b>
	<b>2</b>	Length <b>l<sub>1</sub></b>
	<b>3</b>	Type