



Metric



Metric table

1 d ₁ ±0.2	2 Length l ±0.25						d ₂	For self-tapping screws DIN 7500
	194	244	294	394	-	-		
20 0.79	194 7.64	244 9.61	294 11.57	394 15.51	-	-	4.5 0.18	M 5
28 1.10	192 7.56	242 9.53	292 11.50	392 15.43	492 19.37	592 23.31	5.5 0.22	M 6
30 1.18	189 7.44	289 11.38	389 15.31	489 19.25	589 23.19	989 38.94	3.6 0.14	M 4

Dimensions in: millimeters / inches

Specification

Aluminum

- Powder coated
Black, RAL 9005, textured finish (available up to 3000 mm length)
- Anodized finish, natural color (available up to 2600 mm length)

- SW
- EL

RoHS

On request

- Plastic cover in black or light gray for tube Ø 28 mm

Handle tubes GN 930 with screw channel are designed for use in a variety of different tube handles (e.g. GN 333).

For applications not requiring handle bases, the screw channel provides a very economical mounting solution by using self-tapping screws. The lengths, dimension „Length l“ listed in the table are stock lengths. Depending to the finish, any lengths until max. 3000 mm are available.

see also...

GN 333 Tubular Handles Page QVX

Accessory

GN 333.8 Angled Handle Legs (for Tubes Ø 28 mm) QVX

GN 333.9 Straight Handle Legs (for Tubes Ø 28 mm) QVX

How to order

GN 930-30-989-EL

1	Handle diameter d ₁
2	Length l
3	Finish