



Metric



**2 Type**

- A** Mounting from the back (tapped blind hole)
- B** Mounting from the operator's side

**Metric table**



Dimensions in: millimeters / inches

l <sub>1</sub>		b	d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	l <sub>2</sub>	l <sub>3</sub>	s	t <sub>1</sub> min.	t <sub>2</sub>
GN 728	GN 728.5											
120 4.72	120 4.72	22.5 0.89	M 6	6.4 0.25	11 0.43	42.5 1.67	6.5 0.26	147 5.79	108 4.25	8 0.31	10 0.39	6.5 0.26
180 7.09	-	27 1.06	M 8	8.4 0.33	13.5 0.53	47.5 1.87	7.5 0.30	214 8.43	165 6.50	10 0.39	12 0.47	8.5 0.33

**Specification**



**GN 728**

**Aluminum die-cast**

- Powder coated
- Black, RAL 9005, textured finish
- Silver, RAL 9006, textured finish
- Plain, tumbled finish

- **SW**
- **SR**
- **BL**

**GN 728.5**

**Stainless steel precision casting** AISI CF-8

Matte shot-blasted finish

RoHS

**On request**

- For certain minimum quantities, special colors
- Various metric size fasteners and kit packaging

Economical cabinet U-handles GN 728 and GN 728.5 are a low-cost alternative in metal.

The installation can be carried out from the back (type A) as well as from the operator's side (type B). Hole center dimension is identical in both versions, so they can be mounted in pairs opposite each other. Tumbled finish version not recommended to be anodized.

see also...

**EN 528** Cabinet U-Handles (Plastic, Mounting from the Operator's Side) QVX

**EN 528.1** Cabinet U-Handles (Plastic, Mounting from the Back) QVX

**Technical Information**

Load Capacity Information QVX

Stainless Steel Characteristics QVX

How to order (Aluminum die-cast)

**GN 728-120-A-SW**

- 1** Length l<sub>1</sub>
- 2** Type
- 3** Finish

How to order (Stainless steel precision casting)

**GN 728.5-120-B**

- 1** Length l<sub>1</sub>
- 2** Type

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

