



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

d₁	d₂ Thread	Length l						d₃	d₄	h₁	h₂	s₁	s₂	A/F ^{-0.1 -0.4}	Max. thread length for tapped insert
34 1.34	M 6	11 0.43	15 0.59	20 0.79	25 0.98	30 1.18	16 0.63	6.1 0.24	21 0.83	10.5 0.41	5 0.20	4 0.16	10 0.39	19 0.75	
42 1.65	M 8	15 0.59	20 0.79	25 0.98	30 1.18	40 1.57	19 0.75	8.1 0.32	26 1.02	13 0.51	5 0.20	5 0.20	13 0.51	24 0.94	
42 1.65	M 8 x 1	15 0.59	20 0.79	25 0.98	30 1.18	-	19 0.75	8.1 0.32	26 1.02	13 0.51	5 0.20	5 0.20	13 0.51	24 0.94	
53 2.09	M 10	20 0.79	25 0.98	30 1.18	40 1.57	50 1.97	24 0.94	10.1 0.40	32 1.26	16 0.63	5 0.20	6 0.24	17 0.67	30 1.18	
53 2.09	M 10 x 1	20 0.79	25 0.98	30 1.18	40 1.57	-	24 0.94	10.1 0.40	32 1.26	16 0.63	5 0.20	6 0.24	17 0.67	30 1.18	

Specification

- Knob body
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black, matte finish
- Tapped insert / threaded stud
- Steel, zinc plated, blue passivated finish **ST**
- Stainless steel AISI 304 **NI**
- Cover cap
Plastic
Light gray, matte finish
- *Plastic Characteristics* → page 2135
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

Information

GN 7336 hollow knurled knobs are characterized by their universal application possibilities. With the use of DIN screws and DIN nuts as insert, other thread lengths, left-hand and fine threads and AISI 316 stainless steel variants are possible even in small quantities. The inserts are fixed in the housing with a tight fit by ultrasonic welding.

These knurled knobs are also available without insert and with a removable cover cap, allowing them to be fitted with specific inserts by the user. The insert should be secured axially by a lock nut or a retaining ring at the lower collar of the knurled knob.

see also...

- *Diamond Cut Knurled Knobs EN 534 (with Brass Tapped or Plain Blind Bore Insert)* → page 680
- *Diamond Cut Knurled Knobs EN 534 (with Steel Threaded Stud)* → page 682

On request

- Other thread lengths
- Tapped insert / threaded stud
- in AISI 316 stainless steel
- with left-hand thread
- with other fine threads
- Cover cap in other colors

How to order (Without insert)	1 Handle diameter d ₁
GN 7336-53	
How to order (Tapped insert)	1 Handle diameter d ₁
GN 7336-42-M8-NI	2 Thread d ₂
	4 Material
How to order (Threaded stud)	1 Handle diameter d ₁
GN 7336-34-M6-20-ST	2 Thread d ₂
	3 Length l
	4 Material