


**SS** Stainless Steel

**3 Type**

- MS** Brass tip
- KU** Plastic tip (Polyacetal POM)
- ZK** Ball end



**Metric table**

Dimensions in: millimeters - inches

<b>1</b> $d_1$	<b>2</b> $l_1$ Nominal length	$d_2$	$d_3$	$d_4 + 0.05$	$l_2$	$l_3$	$l_4$	$l_5 \approx$	A/F				
M 6	16* 0.63	20 0.79	25 0.98	30 1.18	35 1.38	4 0.16	3.5 0.14	4.5 0.18	1 0.04	1.3 0.05	4 0.16	5.1 0.20	10 0.39
M 8	20* 0.79	25 0.98	30 1.18	35 1.38	45 1.77	6 0.24	5 0.20	6.1 0.24	1.5 0.06	1.6 0.06	5.3 0.21	6.2 0.24	13 0.51
M 10	25* 0.98	30 1.18	35 1.38	45 1.77	55 2.17	8 0.31	6.5 0.26	7.8 0.31	2 0.08	1.9 0.07	6.4 0.25	7.3 0.29	17 0.67

\* Only available in type MS and KU

**Specification**

- Stainless steel AISI 304
- *Stainless Steel Characteristics* → page QVX
- *Plastic Characteristics* → page QVX
- RoHS compliant

**Information**

GN 933.5 hex head screws with brass or plastic tip are used in applications where markings, pressure dents and damage to the workpiece are unacceptable.

The type ZK has a ball diameter  $d_4$  that is smaller than the core diameter  $d_1$  of the thread. This makes it suitable for use with GN 631 / GN 631.5 thrust pads which need to be ordered separately.

see also...

- *Set Screws GN 913.5 (Stainless Steel)* → page QVX
- *Thrust Pads GN 631 (Plastic)* → page QVX
- *Thrust Pads GN 631.5 (Stainless Steel)* → page QVX

<p>How to order</p> <p><b>GN 933.5-M6-20-KU</b></p>	<b>1</b> Thread $d_1$
	<b>2</b> Thread length $l_1$
	<b>3</b> Type

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10