



**2 Bore code**

**B** Without keyway

**4 Type**

**A** Without handle

**D** With revolving handle

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> d <sub>1</sub>	<b>3</b> d <sub>2</sub> H9	d <sub>3</sub>	d <sub>6</sub>	b	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	l <sub>5</sub>	d <sub>4</sub>	d <sub>5</sub>
125 4.92	10 0.39	55 2.17	32 1.26	18 0.71	15 0.59	22 0.87	28 1.10	65 2.56	47 1.85	23 0.91	M 8
160 6.30	10 0.39	70 2.76	42 1.65	22 0.87	17 0.67	26 1.02	35 1.38	65 2.56	60 2.36	23 0.91	M 8
200 7.87	12 0.47	85 3.35	53 2.09	26 1.02	20 0.79	27 1.06	40 1.57	80 3.15	75 2.95	26 1.02	M 10
250 9.84	12 0.47	105 4.13	68 2.68	30 1.18	22 0.87	30 1.18	49 1.93	80 3.15	99 3.90	26 1.02	M 10

**Specification**

- Plastic  
Duroplast (Phenolic PF)  
- High strength reinforced  
- Black, shiny finish
- Hub bushing  
Steel, blackened finish
- Revolving handles  
Plastic, Duroplast  
- Black, shiny finish  
- Threaded spindle  
Steel, zinc plated
- ISO Fundamental Tolerances → page QVX
- Plastic Characteristics → page QVX
- RoHS compliant

**On request**

- Other modifications such as inch and special metric bores, keyways, set screw holes, etc.

**Information**

EN 940 three spoked handwheels are resistant to solvents, oils, grease and other chemical agents. No mounting hole in rim for handwheel without handle. Handle shipped loose; mounting of handle is required.

see also...

- Three Spoked Handwheels EN 950 → page QVX

How to order

**EN 940-125-B10-A**

<b>1</b>	Handwheel diameter d <sub>1</sub>
<b>2</b>	Bore code
<b>3</b>	Bore diameter d <sub>2</sub>
<b>4</b>	Type