



**3 Type**

- A Blank type
- C With plain blind bore, tol. H7
- D With threaded through bore
- E With threaded blind bore

**Inch table**

<b>1</b> $d_1$	<b>2</b> Blank Type A	<b>2</b> $d_2$ Thread Type D / Type E	<b>2</b> $d_3 + 0.001$ Bore Type C	$d_4$	$h_1$	$h_2$
1.00 25.4	Blank	1/4 x 20	B 1/4	0.50 12.7	0.88 22.4	0.50 12.7
1.50 38.1	Blank	5/16 x 18	B 5/16	0.63 16.0	0.88 22.4	0.38 9.7
2.00 50.8	Blank	3/8 x 16	B 3/8	0.81 20.6	1.00 25.4	0.50 12.7
2.50 63.5	Blank	1/2 x 13	B 1/2	1.00 25.4	1.13 28.7	0.56 14.2
3.00 76.2	Blank	5/8 x 11	B 5/8	1.25 31.8	1.25 31.8	0.63 16.0

Dimensions in: inches - millimeters

**Specification**

- Solid aluminum extrusion 6063-T5, etched and clear anodized finish
- ISO Fundamental Tolerances → page 2129
- Cross Holes GN 110 → page 2042
- RoHS compliant

**On request**

- Cross holes and set screw holes

**Information**

Lightweight yet long-lasting, these CKS hand knobs made from a durable aluminum extrusion are an economical choice for a variety of equipment applications.

see also...

- Hand Knobs CKS (with Steel Threaded Stud) → page 637

How to order	<b>1</b> Handle diameter $d_1$
<b>1</b> <b>2</b> <b>3</b> CKS-1.00-1/4X20-E	<b>2</b> Thread $d_2$ (Bore $d_3$ , Blank)
	<b>3</b> Type