



**3 Type**

**C** With plain blind bore, tol. H9

**Metric table**

Dimensions in: millimeters - inches

Length <b>1</b> <b>2</b>	d <sub>1</sub> Bore	d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>5</sub>	h <sub>6</sub>	h <sub>7</sub>	h <sub>8</sub> ≈	t	Ø Handle
64 2.52	B 6	18 0.71	16 0.63	27 1.06	29 1.14	33 1.30	10 0.39	10 0.39	13 0.51	42.5 1.67	18 0.71	18 0.71
80 3.15	B 6	22 0.87	17 0.67	30 1.18	32 1.26	36 1.42	10 0.39	13 0.51	13 0.51	52.5 2.07	26 1.02	21 0.83
100 3.94	B 8	24 0.94	21 0.83	34 1.34	37 1.46	40 1.57	10 0.39	15 0.59	16 0.63	67.5 2.66	28 1.10	23 0.91
130 5.12	B 10	28 1.10	25 0.98	40 1.57	44 1.73	49 1.93	14 0.55	20 0.79	16 0.63	82.5 3.25	30 1.18	26 1.02
160 6.30	B 10	34 1.34	27 1.06	45 1.77	49 1.93	55 2.17	15 0.59	23 0.91	18 0.71	92.5 3.64	30 1.18	28 1.10

**Specification**

- Crank body  
Plastic  
Technopolymer (Polyamide PA)  
- Special glass fiber reinforced  
- Temperature resistant up to 195 °F (90 °C)  
- Black, matte finish
- Hub bushing  
Steel, blackened finish
- Threaded bushing to accept the revolving handle  
Brass
- Revolving handle GN 598 → page 38  
Plastic  
Technopolymer  
- Black, matte finish  
- Threaded spindle  
Steel, zinc plated, blue passivated finish
- Cross Holes GN 110 → page 2042
- Plastic Characteristics → page 2135
- ISO Fundamental Tolerances → page 2129
- RoHS compliant

**On request**

- Other modifications such as inch and metric bores, squares, keyways, set screw holes, etc.

**Information**

The structure of the crank arm and special technopolymer used make these EN 570 crank handles very strong and therefore suitable for heavy duty cranking applications.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- Crank Handles GN 471 (Aluminum) → page 282
- Crank Handles GN 471.1 (Zinc Die-Cast) → page 282
- Crank Handles EN 670 (Technopolymer Plastic) → www.jwwinco.com
- Crank Handles EN 570.1 (Technopolymer Plastic) → page 291

How to order

**EN570-130-B10-C**

<b>1</b>	Length l
<b>2</b>	Bore d <sub>1</sub>
<b>3</b>	Type