



Inch table

¹ d ₁	² d ₂	³ Length l	Dimensions in: inches - millimeters					
1.25 31.8	1/4 x 20	1.00 25.4	-	-	-	d ₃ 0.50 12.7	h ₁ 0.88 22.4	h ₂ 0.50 12.7
1.50 38.1	5/16 x 18	1.00 25.4	-	-	-	0.63 16.0	1.00 25.4	0.50 12.7
2.00 50.8	5/16 x 18	0.50 12.7	-	-	-	0.88 22.4	1.00 25.4	0.50 12.7
2.00 50.8	3/8 x 16	1.00 25.4	1.50 38.1	2.00 50.8	2.50 63.5	0.88 22.4	1.00 25.4	0.50 12.7
3.00 76.2	5/16 x 18	2.50 63.5	-	-	-	0.88 22.4	1.13 28.7	0.56 14.2

Specification

- Hand knob d₁ = 1.50 / 2.00 / 3.00"
Phenolic plastic
 - Temperature resistant up to 300 °F (149 °C)
 - Black, shiny finish
- Hand knob d₁ = 1.25"
Nylon plastic
 - Temperature resistant up to 200 °F (93 °C)
 - Black, matte finish
- Threaded stud
Steel, zinc plated
- *Plastic Characteristics* → page 2135
- [RoHS compliant](#)

Information

FPKS hand knobs are a popular choice for light duty finger tightening applications. The threaded stud expands the range of clamping operations.

see also...

- *Hand Knobs FPK (with Brass Tapped Insert)* → page 638

On request

- Additional thread sizes and stud lengths

How to order ¹ ² ³ FPKS-2.00-3/8X16-1.50	1 Handle diameter d ₁
	2 Thread d ₂
	3 Length l

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4