



SS Stainless Steel

Inch table



Dimensions in: inches - millimeters

d_1 Fits pin diameter	$b \pm 0.01$	d_2	$d_3 \pm 0.005$	$h_1 \pm 0.01$	$h_2 \pm 0.005$	h_3	$m \pm 0.01$
0.250 6.4	0.625 15.9	6 x 32	0.375 9.5	0.650 16.5	0.060 1.5	0.060 1.5	1.000 25.4
0.313 8.0	0.625 15.9	6 x 32	0.469 11.9	0.783 19.9	0.060 1.5	0.060 1.5	1.000 25.4
0.375 9.5	0.625 15.9	6 x 32	0.562 14.3	0.913 23.2	0.060 1.5	0.060 1.5	1.000 25.4
0.500 12.7	0.875 22.2	10 x 32	0.750 19.1	1.195 30.4	0.100 2.5	0.060 1.5	1.125 28.6

Specification

- Flanged receptacle
Stainless steel AISI 303
- [Stainless Steel Characteristics](#) → page QVX
- [RoHS compliant](#)

On request

- Diamond, rectangular, and round configurations
- Stainless steel 17-4 version
- Other materials and configurations available in certain minimum quantities

Information

FR 100.2 flanged receptacles provide a permanent and proper mating hole for ball lock pins. Designed for use on materials and in applications where the pin does not have anything to lock against. Because the pin does not protrude out of the bottom of the receptacles, they are ideal for blind hole applications.

Can be mounted with screws, rivets or bolts.

see also...

- [T-Handle Ball Lock Pins WN 100.1 \(with Stainless Steel Shank\)](#) → page QVX
- [Ball Lock Pins RP 200.1 \(with Stainless Steel Shank\)](#) → page QVX
- [Ball Lock Pins RP 200 \(with Steel Shank\)](#) → page QVX

How to order	1 Pin diameter d_1
FR100.2-0.375	

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

