




Metric



Metric table

² d ₁	³ d ₂	d ₃	d ₄	l ₁	l ₂	l ₃ ≈	t
16 0.63	M 5	10 0.39	13 0.51	41.5 1.63	15 0.59	2.5 0.10	10 0.39
18 0.71	M 5	10 0.39	14.5 0.57	56 2.20	19 0.75	2.5 0.10	10 0.39
22 0.87	M 6	14 0.55	18.5 0.73	59 2.32	21 0.83	2.5 0.10	12 0.47
24 0.94	M 6	14 0.55	18.5 0.73	74 2.91	27 1.06	2.5 0.10	12 0.47
25 0.98	M 8	16 0.63	20 0.79	84 3.31	30 1.18	2.5 0.10	14 0.55

Dimensions in: millimeters / inches

Specification

Handle

- Plastic, Polyamide (PA)
- Operating temperature up to 194 °F (90 °C)
- Black, matte finish

KT

Tapped spindle

Steel, zinc plated, blue passivated finish

RoHS

Stepped cylindrical revolving handles GN 798.2 are noted for their modern design, and the stepped shape provides the operator with a better grip.

see also...

GN 798 Stepped Cylindrical Revolving Handles

Page

QVX

Technical Information

Plastic Characteristics

QVX

How to order

GN 798.2-KT-24-M6

1	Material
2	Handle diameter d ₁
3	Thread d ₂

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

