



Metric



SS Stainless Steel

Metric table

2

Dimensions in: millimeters / inches

d ₁	d ₂	d ₃	l ₁ ≈ (Arrested)	l ₂	l ₃	l ₄	l ₅	l ₆
22 0.87	M 6	20 0.79	82 3.23	22 0.87	5.5 0.22	73 2.87	13 0.51	7 0.28
24 0.94	M 6	20 0.79	97 3.82	22 0.87	5.5 0.22	88 3.46	13 0.51	7 0.28
25 0.98	M 6	20 0.79	107 4.21	22 0.87	5.5 0.22	98 3.86	13 0.51	7 0.28

Specification

1

Handle

- Plastic, Polyamide (PA)
- Operating temperature up to 194 °F (90 °C)
- Black, matte finish
- Revolving

KT

GN 798.7

Retractable mechanism

- Steel
- Stem, retaining pin, 1.0718 Blackened finish
- Hub Sintered, blackened finish

GN 798.8

Retractable mechanism

- Stainless steel
- Stem, retaining pin, AISI 303
- Hub, AISI 316LHC, sintered

RoHS

Stepped safety retractable handles GN 798.7 / GN 798.8 are suitable for applications where the handle must not remain in the operating position.

In order to bring the handle into the operating position, it has to be pulled up 90° from its retracted position against a torsion spring to a stop, and then it is pushed against spring pressure into its hold position.

By maintaining the forward thrust on the handle, the handwheel can easily be rotated.

When releasing the handle, the spring automatically returns it back to the retracted position.

Technical Information

Page

Plastic Characteristics

QVX

Stainless Steel Characteristics

QVX

How to order (Steel)

GN 798.7-KT-24

- 1 Material
- 2 Handle diameter d₁

How to order (Stainless steel)

GN 798.8-KT-25

- 1 Material
- 2 Handle diameter d₁

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

